



WORLD'S STRONGEST BOND™

Technical Data Sheet

Revised 07/2021

SuperWeld™ Light-Activated Glue

PRODUCT BRIEF

SuperWeld Light Activated Glue is a specially formulated super glue that cures instantly when exposed to blue light. Simply apply the glue, shine the included light, and in 5 seconds the glue will fully cure. Use for bonding objects of all shapes & sizes, filling gaps, and sealing cracks.

Part Number	Container Size
33301	Carded 5g Pen



PRODUCT BENEFITS

- Light curing super glue and applicator for precision application
- Instant cure with light
- 1 minute set, 24 hour cure without light
- Bonds difficult areas and small repairs
- Fills gaps, seals cracks and leaks, and rebuilds surfaces

TYPICAL APPLICATIONS

- Metal & Jewelry, Glass & Beads, Ceramic & Porcelain, Plastic & Vinyl, Wood & More

DIRECTIONS FOR USE

1. **PREPARE SURFACE:** Clear repair area of dirt, grease, oil, paint, rust, etc. For best results use a detergent or degreaser to clean the surface, then roughen surface with file or coarse sandpaper to provide the best repair.
2. **APPLICATION:** Twist on cap to puncture seal. Squeeze pen body to dispense glue.
3. **LIGHT:** Push switch up to turn on the light. Shine light within 1 inch of glue for 5 seconds or until glue is cured.

*Note: If bonding objects where light activator cannot penetrate, or opaque objects, apply thin layer of glue to one surface, press & hold together for 30-60 seconds. Full cure in 24 hours.

VOC STATUS:

Compliant for sale in all 50 states.

DISCLAIMER

**Not recommended for Polyethylene Plastic (PE), Polypropylene Plastic (PPE), Nylon, and other highly flexible materials and non-porous surfaces.*

The information and recommendations contained herein are based on our research and are believed to be accurate, but no warranty, express or implied, is made or should be inferred. Purchasers should test the products to determine acceptable quality and suitability for their own intended use.