

# TR4500HR Treadmill

TR45-0130-13

## Parts Manual


1/5/2019 17:26:03 PM

**Table of Contents**

---


|                                   |   |
|-----------------------------------|---|
| <a href="#">Component 1</a> ..... | 3 |
| <a href="#">Component 2</a> ..... | 4 |
| <a href="#">Component 3</a> ..... | 5 |

## Component 1




| Ref # | Part Number     | Qty | Description                          |
|-------|-----------------|-----|--------------------------------------|
| -     | OK40-01093-0001 | 1   | NLA MONOCOLUMN: BLK-WRINKLE; S/C-C   |
| -     | AK40-00060-0001 | 1   | NLA: OVERLAY/BZL/SW: PURCH; EN+MT D  |
| -     | AK40-00022-0000 | 1   | NLA: CLOSURE-ADAPTER ASSY: PURCH. D  |
| -     | OK40-01186-0003 | 1   | NLA: 76BE: HANDRAIL D                |
| -     | AK40-00037-0003 | 1   | NLA: -MOTOR-COVER ASSY: MFG;TR4500 C |
| -     | 0017-00009-0796 | 1   | Leg Leveler                          |
| -     | AK40-00069-0001 | 1   | HANDLEBAR W/GRIP ASSY: PURCH.D       |
| -     | AK40-00072-0001 | 1   | CONS-ASSY: MFG; ENG+MET; S/C-D       |
| -     | AK40-00035-0000 | 1   | Stop-Key And Clip Assembly: Mfg. C   |
| -     | OK40-01021-0000 | 1   | Wheel: Lift; 2.5 O.D. B              |

## Component 2



| Ref # | Part Number     | Qty | Description                               |
|-------|-----------------|-----|-------------------------------------------|
| -     | AK40-00052-0000 | 1   | ON/OFF Switch                             |
| -     | AK40-00017-0000 | 1   | Cable-Assembly: Display-Console C         |
| -     | SK40-00045-0001 | 1   | Polar HR Kit                              |
| -     | 0017-00103-0197 | 1   | Hardware: Nut 1/2 - Push CA BP D ST NO B  |
| -     | 0017-00101-1239 | 1   | Hardware: 6-20X10 PHL PAN B ST BZ B       |
| -     | AK40-00039-0001 | 1   | NLA: VENT-COVER ASSY: BLACK; MFG. C       |
| -     | AK36-00013-0000 | 1   | Line-Cord Assembly: Domestic. Purchased B |
| -     | OK40-01086-0008 | 1   | NLA: ENDCAP: LT; BLACK S/C-D              |
| -     | OK40-01034-0001 | 1   | Mount: Handrail; Black; S/C-D             |
| -     | 0017-00101-1033 | 1   | Hardware: 10- X 6 PHL PAN AB ST BZ B      |
| -     | 0017-00101-1309 | 2   | Hardware: 10- X32 PHI PAN AB ST BZ B      |
| -     | 0017-00101-1096 | 1   | Hardware: Spring Mounting Screw           |
| -     | 0017-00101-1159 | 1   | Hardware: 10- X 8 PHI PAN 25 ST BZ B      |
| -     | 0017-00032-0191 | 1   | Safety Switch Tab                         |
| -     | OK40-01165-0003 | 1   | NLA: EXTRUSION: TOP; RT+LT                |
| -     | OK40-01095-0001 | 1   | Accessory: Tray: Access; Black 2-Sheet E  |
| -     | OK40-01086-0007 | 1   | NLA: ENDCAP: RT; BLACK S/C-D              |

## Component 3



| Ref # | Part Number     | Qty | Description                                                       |
|-------|-----------------|-----|-------------------------------------------------------------------|
| -     | OK40-01189-0000 | 1   | Clamp: B                                                          |
| -     | OK40-01026-0001 | 1   | Spring: Tecspak, Black S/C-B                                      |
| -     | AK36-00025-0000 | 1   | Cable-Assembly: Home-Switch B                                     |
| -     | GK45-00002-0009 | 1   | Kit: Serv; Actuator-Pin BM                                        |
| -     | OK40-01177-0001 | 1   | Belt: Walking; Siegling C                                         |
| -     | SK40-00051-0001 | 1   | Kit: Serv; Motor; 120/60 BM                                       |
| -     | OK40-01014-0000 | 1   | Belt: Poly-V; 180J8; 18.00" B                                     |
| -     | AK40-00027-0000 | 1   | Front-Roller Assembly: Mfg. B                                     |
| -     | 0017-00101-1611 | 1   | Hardware: Insert Screw                                            |
| -     | AK40-00031-0000 | 1   | Speed-Sensor with Bracket Assembly; Mfg. B                        |
| -     | AK40-00033-0001 | 1   | USE/ AK40-00033-0001R: NC "R & R": HEATSINK/CNTRL ASY: MFG; DOM D |
| -     | 0017-00032-0178 | 1   | Home Switch                                                       |
| -     | OK40-01132-0002 | 1   | NLA: ACTUATOR: LINEAR; DOM. S/C-D                                 |
| -     | OK40-01096-0000 | 1   | NLA: ROD: BELT-TENSIONING B                                       |
| -     | OK40-01013-0000 | 1   | Roller: Rear; Idler D                                             |
| -     | 0017-00003-0751 | 1   | Transformer: Power; Domestic 2-Sheet C                            |
| -     | SK40-00076-0000 | 1   | Kit: Serv; Deck BM                                                |

